







P.C.B LAYOUT



Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10m Ω
- After environmental testing : ≤20mΩ

X3025WV-2x08C-LPSN

①Series No.

②Category :

W-wafer

③Welding Board Angle:

V-180°

④Welding Way:

Blank-DIP

⑤Row No.-Pin No.

2*XX-Double row

⑥Special NO.

C- The harpoon

⑦Material:

LP-LCP 94V-0 N0-PA9T 94V-0

⑧Planting Category:

V**All Gold-Plated
*01-Gold Flash ; *02-2u" ; *03-3u" ; *05-5u"
*10-10u" ; *15-15u" ; *30-30u" ; *50-50u"
SN-Bright tin plating 70u"
SN1-Bright tin plating 120u"Min. ;
SW-Fog Tin plating

⑨Color :

Blank-natural color

Poles	Dimensions (mm)	
	A	B
02	-	6.65
04	3.00	9.65
06	6.00	12.65
08	9.00	15.65
10	12.00	18.65
12	15.00	21.65
14	18.00	24.65
16	21.00	27.65
18	24.00	30.65
20	27.00	33.65
22	30.00	36.65
24	33.00	39.65

X3025WV-2x08C-LPSN	LCP UL 94V-0	Brass	Tin Plating Fog	X3025H
X3025WV-2x08C-N0SN	Nylon 9T UL 94V-0			
PART NO	Material	Material (Pin)	Finish (Pin)	Mates WithXKB Housing

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX				XKB	ANGULAR ±5°
ΔX					L ≤4 ±0.2
ΔX					4<L ≤16 ±0.3
ΔX					16<L ≤63 ±0.4
ΔX					L >63 ±0.5

DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors
DWN		DATE		VIEW:	PART NO.: X3025WV-2x08C-LPSW
CHKD		DATE		UNIT: mm/in	DWG NO.: X3025WV-2x08C-LPSW
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0