




Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:800V AC/minute

耐受电压: 800V AC/分钟

Temperature range:-25℃-+85℃

温度范围: -25℃-+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

X2026 H -2x06B-N0

① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

2.Category:H-HSG

3.Appearance type:Blank-Ordinary

4.Row No-Pin No:2xXX-2x02P~2x22P

5.Plug the Pin&Special N0:

B-With Lock In the middle

6.Material:N0-PA66 94V-0

7.Color:Blank-Natural Color;BK-Black

poles	Dimensions(mm)			poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	5.90	4.60	2x10	18.00	21.90	20.60	2x18	34.00	37.90	36.60
2x03	4.00	7.90	6.60	2x11	20.00	23.90	22.60	2x19	36.00	39.90	38.60
2x04	6.00	9.90	8.60	2x12	22.00	25.90	24.60	2x20	38.00	41.90	40.60
2x05	8.00	11.90	10.60	2x13	24.00	27.90	26.60	2x21	40.00	43.90	42.60
2x06	10.00	13.90	12.60	2x14	26.00	29.90	28.60	2x22	42.00	45.90	44.60
2x07	12.00	15.90	14.60	2x15	28.00	31.90	30.60				
2x08	14.00	17.90	16.60	2x16	30.00	33.90	32.60				
2x09	16.00	19.90	18.60	2x17	32.00	35.90	34.60				

X2026H-2x06B-N0BK	Nylon 66 UL 94V-0(Black)	X2026T-B	X2026W-B
X2026H-2x06B-N0	Nylon 66 UL 94V-0		
PART NO	Material	Suitable XKB Terminal	Suitable XKB Wafer

Wire to board connector

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.00mm Crimp Style Connectors		
					units:	mm	DWN		DATE		VIEW: 	PART NO.: X2026H-2x06B-N0		
Δ x							CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2026H-2x06B-N0		
Δ x					X.X	±0.2mm	APPD		DATE		SIZE: A4	WEIGHT 1.0g	SHEET 1/1	REVISION A0
Δ x					X.XX	±0.1mm								
Δ x					X.XXX	±0.05mm								
MARK	DESCRIPTION				DATE	REVISED	APPROVED							
REVISIONS							UNSPECIFIED TOLERANCES							
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED							

					units: mm
ΔX					tolerance:
ΔX					X.X ±0.2mm
ΔX					X.XX ±0.1mm
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX ±0.05mm

REVISIONS

UNSPECIFIED TOLERANCES