

1



2

3

4

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图框升级整理图面	2024.08.03	阿 树






■SPECIFICATIONS

- Voltage rating:600V AC/DC
- Current rating:7A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ

PART NO.:

X9357 W R-2x08 ES-N2 SN
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
- ② Category:W-Wafer
- ③ Welding Board angle:R-Stright 90°
- ④ Row No.Pin No:2xXX-2x01P~2x12P
- ⑤ Plug the Pin&Specal NO.:
ES-With Ears and Screw Holes
- ⑥ Material:N2-PA66 94V-2
- ⑦ Plating:SN-Bright tin plating



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x01		5.40	2x07	25.20	30.60
2x02	4.20	9.60	2x08	29.40	34.80
2x03	8.40	13.80	2x09	33.60	39.00
2x04	12.60	18.00	2x10	37.80	43.20
2x05	16.80	22.20	2x11	42.00	47.40
2x06	21.00	26.40	2x12	46.20	51.60

X9357WR-2x08ES-N2SN	Nylon 66 UL 94V-2	Brass	Tin-Plated	X9357H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	阿 树	VIEW:	MODEL TYPE: 4.20 mm Crimp Style Connector		
CHECKED		UNIT: mm/in	PART NO.: X9357WR-2x08ES-N2SN		
APPROVED		SIZE: A4	DWG NO.: X-X9357WR-2x08ES-N2SN		
PRECISION CO.,LIMITED			SCALE	PAGE	REVISION
			N/A	1 / 1	A1

1

2

3

4