

1

2

3

4

A

A

B




B

C




C

D

D




PCB WELDING DRAWING



CIRCUIT DIAGRAM

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.26	阿树



SPECIFICATION
Contact Rating: 50mA, 12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100MΩ min. 500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.20mm
Operating Temp: -20℃~+70℃
Storage Temp: -30℃~+80℃

PAPT NO	TC-1101V-B-A-W
Operating Force	A:100gf B:160gf C:260gf
Height	Code-X
Colour	B:black W:white

⑤	Terminal	2	Brass (0.30t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	PPA	
②	Cover	1	Spcc	Plating Nickel
①	Keystake	1	PPA	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	TACT SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	TC-1101V-B-A-W
APPROVED		SIZE:	A4	DWG NO.:	

XKB INDUSTRIAL PRECISION CO., LIMITED

TC-1101V-B-A-W	SCALE	PAGE	REVISION
N/A	N/A	1/1	A1

1

2

3

4