





Specifications:

规格:

Voltage rating:350V AC/DC

额定电压: 350V AC/DC

Current rating:4A AC/DC

额定电流: 4A AC/DC

Withstanding voltage:1700V AC/minute

耐受电压: 1700V AC/分钟

Temperature range:-25℃-+85℃

温度范围: -25℃-+85℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:10mΩ Max

接触电阻: 20mΩ Max

X1801 H - 02 L - N0
① ② ③ ④ ⑤

1.Series No

2.Category:H-HSG

3.Row No-Pin No:02Pin

4.Special No:L-With Lock

5.Material:N0-Nylon66 , UL94V-0(White)

X1801H-02L-N0	Nylon66	X1801W	X1801T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

					ANGLAR	±5°
Δ x					L≤ 4	±0.2
Δ x					4<L≤ 16	±0.3
Δ x					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE: 1.8mm Crimp Style Connector	
DWN	VIEW:	PART NO.: X1801H-02L-N0	
CHKD	UNIT: mm/in	DWG NO.: X-X1801H-02L-N0	
APPD	SIZE: A4	WEIGHT	SHEET
		1/1	REVISION A0