




■ Specifications :



- Voltage rating: 350V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -55°C~+105°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤20mΩ
- After environmental testing : ≤40mΩ

X1511 W V S-14 HF-LP SW

- ① Series No.
② Category : W-WAFER
③ Welding Board Angle : V-Straight 180°
④ Welding Way:S-SMT
⑤ Row No.-Pin No.: XX-02P~15P
⑥ Plug the Pin & Special NO.:HF-Halogen free
⑦ Material : 9T-PA9T;46-PA46;LP-LCP 94V-0
⑧ Planting Categoty:SW-Matte Tin Plating



PCB LAYOUT



Poles	Dimensions(mm)		
	A	B	C
02	1.50	4.30	3.70
03	3.00	5.80	5.20
04	4.50	7.30	6.70
05	6.00	8.80	8.20
06	7.50	10.30	9.70
07	9.00	11.80	11.20
08	10.50	13.30	12.70
09	12.00	14.80	14.20
10	13.50	16.30	15.70
11	15.00	17.80	17.20
12	16.50	19.30	18.70
13	18.00	20.80	20.20
14	19.50	22.30	21.70
15	21.00	23.80	23.20

X1511WVS-14HF-LPSW	LCP UL 94V-0 Halogen Free	Brass	Matte Tin Plating	X1511T
PART NO	Material	Material(Pin&Solder Tab)	Finish(Pin)	Suitable XKB Terminal

						DSND		DATE		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connectors						
					ANGLAR	±5°	DWN		DATE	VIEW: 	PART NO.: X1511WVS-14HF-LPSW						
Δx					L ≤ 4	±0.2	CHKD		DATE	UNIT: mm/in	DWG NO.: X-X1511WVS-14HF-LPSW						
Δx					4<L ≤ 16	±0.3											
Δx					16<L ≤ 63	±0.4											
MARK	DESCRIPTION				DATE	REVISED	APPROVED	L > 63	±0.5	APPD		DATE		SIZE: A4	X-K1511WVS-14HF-LPSW		
REVISIONS						UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED						
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn																	
											WEIGHT	SHEET	REVISION				
											1.0g	1/1	A0				