



Recommended PCB
Layout ±0.05



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:10A AC/DC

额定电流: 10A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:10mΩ Max

接触电阻: 10mΩ Max

X5050 W R - 04 B - 4T SN
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:R-Stright 90°
- 4.Row No.Pin No:04Pin
- 5.Special No:B-With Buckle the poi sitive angle
- 6.Material:4T-Nylon 4T UL94V-0 ;
9T-Nylon 9T UL94V-0; N2-Nylon 66 UL94V-2
- 7.Plating:SN-Bright Tin Plated

X5050WR-04B-N2SN	Nylon 66 UL 94V-2	Brass (Tin Plated)	Staninless Steel(Tin Plated)	X5050H
X5050WR-04B-9TSN	Nylon 9T UL 94V-0			
X5050WR-04B-4TSN	Nylon 4T UL 94V-0			
PART NO	Material	Material(Pin)	Material(MetalBand)	Suitable XKB Housing

					ANGLAR	±5°
Δ x					L≤ 4	±0.2
Δ x					4<L≤ 16	±0.3
Δ x					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE: 5.08mm Crimp Style Connector
DWN	VIEW:	PART NO.: X5050WR- 04B-4TSN
CHKD	UNIT: mm/in	DWG NO.: X-X5050WR- 04B-4TSN
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0