

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.12	阿树

■SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating:3A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥500MΩ
- Contact resistance:≤10mΩ
- After environmental testing:≤20mΩ

PART NO.:

X2508 W V-02-N0 SN XX
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Row No.Pin No:XX-02~15Pin
⑤Material:N0-PA66 94V-0;N2-PA66 94V-2
⑥Planting:SN-Bright Tin Plating
SN1-Bright Tin Plating
SW-Matte Tin Plating
⑦Color:Blank-natural color;

POLES	A	B	C	POLES	A	B	C
2	7.50	5.80	2.50	9	25.00	23.30	20.00
3	10.00	8.30	5.00	10	27.50	25.80	22.50
4	12.50	10.80	7.50	11	30.00	28.30	25.00
5	15.00	13.30	10.00	12	32.50	30.80	27.50
6	17.50	15.80	12.50	13	35.00	33.30	30.00
7	20.00	18.30	15.00	14	37.50	35.80	32.50
8	22.50	20.80	17.50	15	40.00	38.30	35.00


X2508WV-02-N0SN	Nylon 66 UL 94V-0	Brass	Tin Plated	X2508H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 2.50mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.: X2508WV-02-N0SN
APPROVED		SIZE:	A4	DWG NO.: X-X2508WV-02-N0SN

SCALE	PAGE	REVISION
N/A	1/1	A1



Recommand PCB Layout