

1

2

3

4


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	

A


B

C

D



产品字码标识



ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED


规格 Specification:

- 1.额定值 Rating:8A 125/250VAC
- 2.接触电阻 Contact resistance:≤30 mΩ
- 3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
- 4.电气寿命 Electronics life:>10000 cycles
- 5.操作力 Operation force:500±200gf
- 6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 08 23 P L-10 R 3 B B
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;
- ② Enclosure Material:
A-Metal case;
BLANK-Plastic case;
- ③ Current Rating: 08-08A;
- ④ Switch Circuit:23-2P3T;
- ⑤ P: Welding plates;
- ⑥ Handle Shape: L-Flat handle;
- ⑦ Handle Height: 3~10mm;
- ⑧ Enclosure Shape:R-Locking rings enclosure;
- ⑨ Terminal specs:
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;
- ⑩ Handle Colour:
B-Black; W-White; R-Red
- ⑪ Housing Colour:
B-Black; W-White; R-Red



DESIGN	桑 葚	VIEW:		MODEL TYPE:	SLIDE SWITCH		
CHECKED		UNIT:	mm/in	PART NO.:	SS-0823PL-10R3BB		
APPROVED		SIZE:	A4	DWG NO.:	X-SS-0823PL-10R3BB		
PRECISION CO.,LIMITED				SCALE	PAGE	REVISION	
				N/A	1/1	A0	

1

2

3

4