



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2025.12.22	
A2	ECN-P-2026030301	②X1		2026.03.03	



02P

03~06P




■SPECIFICATIONS

- Voltage rating:600V AC/DC
- Current rating:9A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥ 1000MΩ
- Contact resistance:≤20mΩ

PART NO.:


X9357 W R-05 S-N2 SN

Series No
Category:W-Wafer
Welding Board Angle:R-Stright 90°
Row No.Pin No:XX-02~06Pin
Special NO.: S-With positioning column
Material:N0-PA66 94V-0; N2-PA66 94V-2
Planting:SN-Bright tin plating;V30-Gold 30u”



P.C.B. Layout
02P

P.C.B. Layout
03~06P



Poles	Dimensions(mm)	
	A	B
02	4.20	9.80
03	8.40	14.00
04	12.60	18.20
05	16.80	22.40
06	21.00	26.60

X9357WR-05S-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X9357H
X9357WR-05S-N2SN	Nylon 66 UL 94V-2		Gold-Plated	
X9357WR-05S-N2V30				
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: 4.20 mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X9357WR-05S-N2SN
APPROVED		SIZE: A4	DWG NO.: