



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.22	阿树

A



Specifications:

规格:

Voltage rating:50V AC/DC

额定电压: 50V AC/DC

Current rating:0.5A AC/DC

额定电流: 0.5A AC/DC

Withstanding voltage:250V AC/minute

耐受电压: 250V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:500MΩ

绝缘电阻: 500MΩ

Contact resistance:100mΩ

接触电阻: 100mΩ

PART NO.:

X0815 W V S-70 D S-9T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

①Series No

②Category:W-Wafer

③Welding Board Angle:V-Stright 180°

④Welding Way: S-SMT

⑤Row No,Pin No:XX-30-80Pin

⑥Category:D-4.8mm Height



⑦Special No:S-With positioning column

⑧Material:9T-PA9T UL94V-0

CAP Material:PA6T UL94V-0


⑨Plating:Gold Plated 3u" MIN

B



Poles	Dimensions(mm)				
	A	B	C	D	E
30	11.20	13.00	14.40	16.30	16.10
40	15.20	17.00	18.40	20.30	20.10
50	19.20	21.00	22.40	24.30	24.20
60	23.20	25.00	26.40	28.30	28.10
70	27.20	29.00	30.40	32.30	32.10
80	31.20	33.00	34.40	36.30	36.10

C



D

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	0.8mm BTB Connector
CHECKED		UNIT:	mm/in	PART NO.:	X0815WS-70DS-9TV01
APPROVED		SIZE:	A4	DWG NO.:	

A

B

C

D