


- Voltage rating: 250V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000\text{M}\Omega$
- Contact resistance: $\leq 20\text{m}\Omega$
- After environmental testing: $\leq 30\text{m}\Omega$

① ② ③ ④

- ① SeriesNumber
② Category : H-HSG
③ Row No.Pin No:xx-02-15P
④ Material:N0-PA66 UL 94V-0



Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.20	5.10	10	18.00	22.20	21.10
03	4.00	8.20	7.10	11	20.00	24.20	23.10
04	6.00	10.20	9.10	12	22.00	26.20	25.10
05	8.00	12.20	11.10	13	24.00	28.20	27.10
06	10.00	14.20	13.10	14	26.00	30.20	29.10
07	12.00	16.20	15.10	15	28.00	32.20	31.10
08	14.00	18.20	17.10	16			
09	16.00	20.20	19.10				

X2012H-10-N0	PA66 UL 94V-0	X2012T	X2012W
PARY N0	Matrial	Suitable XKB Terminal	Suitable XKB Wafer

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connectors		
Δx					ANGULAR	$\pm 5^\circ$	DWN		DATE		VIEW: 	PART NO.: X2012H-10-N0		
Δx					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2012H-10-N0		
Δx					$4 < L \leq 16$	± 0.3	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION		DATE	REVISED	APPROVED	$16 < L \leq 63$								
						$L > 63$								
REVISIONS						UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
www.xk-dc.cn www.helloxkb.com www.helloxkb.cn												1.0a	1/1	A0