


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A2	N/A		PIN	2024.12.10	
A3	N/A	A3 X2		2025.09.05	




- Specifications:
- 1.Voltage rating:250V AC/DC
250V AC/DC
 - 2.Current rating:3A AC/DC
:3A AC/DC
 - 3.Withstanding voltage:500V AC/minute
:500V AC/
 - 4.Temperature range:-55 ~+105
:-55 ~+105
 - 5.Insulation resistance: $\geq 1000M\Omega$
: $\geq 1000M\Omega$
 - 6.Contact resistance: $\leq 30m\Omega$
: $\leq 30m\Omega$
 - 7.Rubber core:PBT UL94V-0
PBT UL94V-0
 - 8.The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
SPCC-SD / /
 - 9.Terminal:Copper alloy


PART NO.:

X04 15 W I Z W 1

Series No
Row No-Pin No 15Pin
Welding Board Angle:W-Male
T:Tradutional C:Car-pin
Planting Category:
1:1u 2:2u 3:3u 4:5u 5:15u 6:30u 7:AuSn
Color:B-Black W-White BL-Blue
1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4



AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	



DESIGN	VIEW:	MODEL TYPE: D-SUB
CHECKED	UNIT: mm/in	PART NO.: X0415WT7W1
APPROVED	SIZE: A4	DWG NO.: