


A		B				C		D		E			
PIN NO		PIN	DIM A	DIM B	DIM C	DIM D	DIM E	REV.	DESCRIPTION	ECN NO.	NAME	DATE	
1	B0510MAA08-8P	8	1.50	2.50	4.70	3.40	4.00						
	B0510MAA08-10P	10	2.00	3.00	5.20	3.90							
	B0510MAA08-12P	12	2.50	3.50	5.70	4.40							
	B0510MAA08-14P	14	3.00	4.00	6.20	4.90							
2	B0510MAA08-16P	16	3.50	4.50	6.70	5.40							
	B0510MAA08-18P	18	4.00	5.00	7.20	5.90							
	B0510MAA08-20P	20	4.50	5.50	7.70	6.40							
	B0510MAA08-22P	22	5.00	6.00	8.20	6.90							
3	B0510MAA08-24P	24	5.50	6.50	8.70	7.40							
	B0510MAA08-26P	26	6.00	7.00	9.20	7.90							
	B0510MAA08-28P	28	6.50	7.50	9.70	8.40							
	B0510MAA08-30P	30	7.00	8.00	10.20	8.90							
4	B0510MAA08-32P	32	7.50	8.50	10.70	9.40	8.00						
	B0510MAA08-34P	34	8.00	9.00	11.20	9.90							
	B0510MAA08-36P	36	8.50	9.50	11.70	10.40							
	B0510MAA08-38P	38	9.00	10.00	12.20	10.90							
5	B0510MAA08-40P	40	9.50	10.50	12.70	11.40							
	B0510MAA08-44P	44	10.50	11.50	13.70	12.40							
	B0510MAA08-50P	50	12.00	13.00	15.20	13.90							
	B0510MAA08-60P	60	14.50	15.50	17.70	16.40							
	B0510MAA08-70P	70	17.00	18.00	20.20	18.90							
	B0510MAA08-80P	80	19.50	20.50	22.70	21.40							
	B0510MAA08-100P	100	24.50	25.50	27.70	26.40							

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN®	
DIM. x.x x.xx x.xxx GENERAL ANGLE: ±1.0°		TITLE: 0.5 Pitch双槽立式BTB公(单高0.8)						
		DWG. NO.: B0510MAA08-XP			CHECKED: MAX			
		PART NO.: B0510MAA08-XP			DRAWN: ELLA			
UNIT: mm	SCALE: none	SHEET: 1 of 2	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL			