





Poles	Dlmentslons(mm) A
2*02	5.08
2*03	7.62
2*04	10.16
2*05	12.70
2*06	15.24
2*07	17.78
2*08	20.32
2*09	22.86
2*10	25.40
2*12	30.48
2*14	35.56
2*16	40.64
2*20	50.80
2*21	53.34
2*24	60.96
2*25	63.50



Recommended P.C.B
Layout(±0.05)

Technical Data
Pin(outer sleeve):Brass,machined CuZn38Pb2
Insulator:PPS UL94V-0 colour:black
Current rating:3Amps
Mating pin Ø:0.62/0.50mm
Mechanical life:min 500cycles
Contact resistance:max 10m Ω
Dielectric strength:min 1000V RMS
Operaling temperature:-40°C to+105°C
Soldering temperature:+255°C

X5621 W V-2x05-C762 D1220
① ② ③ ④ ⑤ ⑥

- ① Series.N0.
- ② Category : W-Wafer
- ③ Welding Board Angle : V-Straight 180°
- ④ Row No-Pin No:2*XX-03,04,05,06,07,08,09,10,12,14,16,20,21,24,25
- ⑤ Plastic Height :C=7.62mm
- ⑥ Pin Length :D:1220=12.2mm;42=4.2mm;74=7.40mm;7.43=7.43mm;92=9.20mm;1020=10.20mm;1120=11.20mm;1150=11.50mm;1170=11.70mm;1390=13.9mm;1340=13.40mm1370=13.70mm;1420=14.20mm;1520=15.20mm;1620-16.20mm1780=17.80mm;1820=18.20mm

X5621WV-2x05-C762D1220	PPS 94V-0	Brass	Tin Gold 1u"	X5621F
PART NO	Material	Material(Terminal)	Finish(Terminal)	Mates With XKB Pin Header

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.54mm BTB Style Connector			
					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X5621WV-2x05-C762D1220			
ΔX					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X5621WV-2x05-C762D1220			
ΔX					4<L ≤ 16	±0.3									
ΔX					16<L ≤ 63	±0.4	APPD		DATE		SIZE: A4				
MARK	DESCRIPTION			DATE	REVISED	APPROVED									L > 63
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn													1.0g	1/1	A0