




NOTES:

1.) MATERIAL:

1-1. HOUSING:LCP,UL 94V-0,COLOR:BLACK;

1-2. CONTACT:C2680 T=0.20;

1-3. SHELL:SPCC ,T=0.50;

2.) FINISH:

2-1. CONTACT: Au G/F PLATING ON CONTACT AREA,(SEE P/N DESCRIBING) MATTE PURE Sn 50u" Min. PLATING ON SOLDER TAILS

2-2. SHELL: PLATING Ni 50u Min

3.) SPECIFICATIONS:

3-1. VOLTAGE RATING: 40V

3-2. CURRENT RATING: 0.5A


3-3. INSULATION RESISTANCE: 100MEG.OHM MIN

3-4. CONTACT RESISTANCE: 10 MILL.OHM MAX

3-5. OPERATION TEMPERATURE: -20°C TO +85°C

3-6. INSERT FORCE: 44.1N MAX

3-7. EXTRACT FORCE: 9.8~39.2N

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. X.X: ±0.25 X.XX: ±0.15 X.XXX: ±0.10 GENERAL ANGLE: .X': ±1.0' .XX': ±0.5'		TITLE: HDMI 19P						
		DWG. NO.: HDMI-04			CHECKED: MAX			
		PART NO.: HDMI-04			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	