



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2024.07.20	阿 树
A2	N/A		产品图面修正	2026.02.03	阿 树




- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:5A AC/DC
 - Withstanding Voltage:1000V AC/minute
 - Temperature range:-45°C+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤10mΩ
 - After environmental testing: ≤20mΩ

PART NO.:

X3025 W V-2x03 C-LP SN
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Row No-Pin No: 2xXX-2x01P~2x12P
⑤Special NO:C-The harpoon
⑥Material: LP-LCP UL94V-0 Black
NO-PA66 UL94V-0
⑦Planting:SN-Bright tin 100u"Min;Ni 50"Min

Poles	Dimensions (mm)	
	A	B
2x01	---	6.65
2x02	3.00	9.65
2x03	6.00	12.65
2x04	9.00	15.65
2x05	12.00	18.65
2x06	15.00	21.65
2x07	18.00	24.65
2x08	21.00	27.65
2x09	24.00	30.65
2x10	27.00	33.65
2x11	30.00	36.65
2x12	33.00	39.65



P.C.B LAYOUT

X3025WV-2x03C-LPSN	LCP UL 94V-0	Brass	Tin Plating Fog	X3025H
X3025WV-2xXXC-N0SN	Nylon 9T UL 94V-0			
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN	阿 树	VIEW:	MODEL TYPE: 3.00 mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X3025WV-2x03C-LPSN
APPROVED		SIZE: A4	DWG NO.: