

1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.03.03	阿树

A

A

B


B

C

C

D

D



PART NO.:

X1002 H-14 B1-N0 HF
① ② ③ ④ ⑤ ⑥


- ①Series No
②Category:H-HSG
③Row No.Pin No:XX-02~20Pin
④Plug the Pin&special No:
B-Ultra-thin hook
⑤Material:NO-PA66 94V-0
⑥Color:Blank-Natural Color
HF-Halogen Free

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

Specifications:

规格:

Voltage rating: 125V AC/DC
额定电压: 125V AC/DC
Current rating: 1A AC / DC
额定电流: 1A AC / DC
Withstanding voltage: 500V AC/minute
耐压电压: 500V AC/minute
Temperature range: -25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance: ≥100MΩ
绝缘电阻: ≥100MΩ
Contact resistance: ≤20mΩ
接触电阻: ≤20mΩ
After environmental testing: ≤40mΩ
环境测试后: ≤40mΩ



03P~20P

02P

poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.00	3.00	2.40	12	11.00	13.00	12.40
03	2.00	4.00	3.40	13	12.00	14.00	13.40
04	3.00	5.00	4.40	14	13.00	15.00	14.40
05	4.00	6.00	5.40	15	14.00	16.00	15.40
06	5.00	7.00	6.40	16	15.00	17.00	16.40
07	6.00	8.00	7.40	17	16.00	18.00	17.40
08	7.00	9.00	8.40	18	17.00	19.00	18.40
09	8.00	10.00	9.40	19	18.00	20.00	19.40
10	9.00	11.00	10.40	20	19.00	21.00	20.40
11	10.00	12.00	11.40				

X1002H-14B1-N0	PA66 UL 94V-0	X1002T-A	1002W
X1002H-14B1-NOHF	PA66 UL 94V-0 Halogen Free	X1002T-A	1002W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Wafer



DESIGN	阿树	VIEW:	MODEL TYPE: 1.00mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X1002H-14B1-NOHF
APPROVED		SIZE: A4	DWG NO.: X-X1002H-14B1-NOHF

1

2

3

4