







Recommended PCB Layout(Top view)
Tolerance:±0.05mm



Specifications:

规格:

Voltage rating:125V AC/DC

额定电压: 125V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-25℃~+105℃

温度范围: -25℃~+105℃

Insulation resistance:≥100MΩ

绝缘电阻: ≥100MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

X9821 W V - 02 R - LP SN
① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Stright 180°

4.Row No.Pin No:XX-02~16Pin

5.Special No:R-DIP 2.3mm

6.Material:LP-LCP UL94V-0 ,Natural

CAP:LCP UL94V-0 ,Natural

7.Plating:SN- Tin Plated

Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
02	1.25	3.20	4.25	10	11.25	13.20	14.25
03	2.50	4.45	5.50	11	12.50	14.45	15.50
04	3.75	5.70	6.75	12	13.75	15.70	16.75
05	5.00	6.95	8.00	13	15.00	16.95	18.00
06	6.25	8.20	9.25	14	16.25	18.20	19.25
07	7.50	9.45	10.50	15	17.50	19.45	20.50
08	8.75	10.70	11.75	16	18.75	20.70	21.75
09	10.00	11.95	13.00				

X9821WV-02R-LPSN	LCP	Brass	X9821HM
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN	VIEW:	PART NO.: X9821WV-02R-LPSN
CHKD	UNIT: mm/in	DWG NO.: X-X9821WV-02R-LPSN
APPD	SIZE: A4	

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5

REVISIONS

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

UNSPECIFIED TOLERANCES

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0