






1. 做用温度: $-25\sim+85^{\circ}\text{C}$;
2. 额定负荷: DC 12V 50mA;
3. 接触电阻: $\leq 50\text{m}\Omega$;
4. 绝缘电阻: $\geq 100\text{M}\Omega$;
5. 耐 压: AC250V (50Hz)/min;
6. 动 作 力: $260\text{g}\pm 50\text{g}$;
7. 使用寿命: 100000次;

按钮A			按钮B		
高度 L_a	帽头 H_a	直径 A_a	高度 L_b	帽头 H_b	直径 A_b
3.15	4.3	Ø3.5	3.15	4.3	Ø3.5
3.85	5.0	Ø3.5	3.85	5.0	Ø3.5
4.35	5.5	Ø3.3	4.35	5.5	Ø3.3
4.85	6.0	Ø3.3	4.85	6.0	Ø3.3
5.35	6.5	Ø3.3	5.35	6.5	Ø3.3
5.85	7.0	Ø3.3	5.85	7.0	Ø3.3
6.35	7.5	Ø3.3	6.35	7.5	Ø3.3
6.85	8.0	Ø3.3	6.85	8.0	Ø3.3
7.35	8.5	Ø3.2	7.35	8.5	Ø3.2
7.85	9.0	Ø3.2	7.85	9.0	Ø3.2
8.35	9.5	Ø3.2	8.35	9.5	Ø3.2
8.85	10.0	Ø3.2	8.85	10.0	Ø3.2
9.35	10.5	Ø3.0	9.35	10.5	Ø3.0
...	...	...	...	...	...
13.85	15.0	Ø3.0	13.85	15.0	Ø3.0
...	>15.0	Ø3.0	...	>15.0	Ø3.0



TC - 0816 * - NH - *G - F* * - 05

A6.8B6.8=A6.8mm, B6.8mm

页次 SHEET	1/
-------------	----