








SPECIFICATIONS:

- 1.VOLTAGE/CURRENT RATING: 30V/AC, DC,0.3A;
- 2.WITHSTANDING VOLTAGE: 100V AC/ONE MINUTE;
- 3.INSULATION RESISTANCE: 50M Ω MIN/100V DC.;
- 4.CONTACT RESISTANCE: 90m Ω MAX./1mA,20mV AC,1KHz;
- 5.DURABILITY: 30 CYCLES;
- 6.OPERATING TEMPERATURE RANGE: -40° C TO 125° C.

MATERIAL:

- 1.INSULATOR: LCP UL 94V-0 BLACK;
- 2.TERMINAL: PHOSPHOR BRONZE;

PLATING:

- 1.TERMINAL: CONTACT AREA: GOLD 0.05 μ m"MIN.
SMT LEAD: GOLD 0.025 μ m" MIN.
UNDERPLATING: NICKEL 1 μ m" MIN.




PIN NO.	DIM A	DIM B	DIM C
10	3.52	1.60	1.00
12	3.92	2.00	1.00
20	5.52	3.60	1.00
24	6.32	4.40	1.20
30	7.52	5.60	1.50
34	8.32	6.40	2.30
40	9.52	7.60	3.20
50	11.52	9.60	3.20
60	13.52	11.60	3.20
70	15.52	13.60	3.20
80	17.52	15.60	3.20
90	19.52	17.60	3.20
100	21.52	19.60	3.20
120	25.52	23.60	3.20

Ordering Information

HC-PBB40C - NDP - 0.4V

No. of Pins	Nature	PITCH
10~120Pin	DP=Male	0.4V=0.4mm
10~10Pin		
12~12Pin		
.....		

			GENERAL TOLERANCE		制 图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD					
			DIM	TOL	审 核 CHECK		产品名称 TITLE		0.4 双槽 立贴 公座 (BTB)	版 本 REV.	A
			X. X	±0.30	批 准 APPROVAL		产品料号 PART NO.		HC-PBB40C-NDP-0.4V	单 位 UNITS	mm
1	初版发行		X. XX	±0.20	比 例 SCALE						
			X. XXX	±0.10	投 影 Projection		材 料 MATERIAL			页 次 SHEET	1/2
序号 No.	变更内容 MODIFY CONTENT		日 期 MODIFY DATE	Angle ±3.0°							



120				
100	44.00	40.40	20.20	5000
90				
80				
70	32.00	28.40	14.20	5000
60				
50	24.00	--	11.50	5000
40				
34				
30				
24	16.00	--	7.50	5000
20				
10	12.00	--	5.50	5000
POS NO.	DIM W	DIM B	DIM F	QTY/REEL

			GENE RL TOLERANCE		制 图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审 核 CHECK					
			X. X	±0.30	批 准 APPROVAL		产品名称 TITLE	0.4 双槽 立贴 公座 (BTB) 包装图	版 本 REV.	A
			X. XX	±0.20	比 例 SCALE		产品料号 PART NO.	HC-PBB40C-NDP-0.4V	单 位 UNITS	mm
1	初版发行		X. XXX	±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	2/2
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle	±3.0°						