




- Notes:
- 1. Material:
 - 1.1 Housing: thermoplastic high temp. UL94V-0;
 - 1.2 Terminal: copper alloy.
 - 1.3 Fitting Nail: copper alloy.
 - 2. FINISH:
 - 2.1 Terminal:
 - 50u"Min Nickel under plating over all
 - I:1u"Gold on contact and solder area.
 - M:5u"Gold on contact and 1u"Gold on solder area.
 - R:10u" Min Gold on contact and 1u"Gold on solder area.
 - S:15u"Gold on contact and 1u"Gold on solder area.
 - 2.2 Fitting Nail:
 - 50u"Min Nickel under plating over all
 - 80~150u" Matte-Tin over all.
 - 3. Product must comply HF RoHS specification.
 - 4. MECHANICAL PERFORMANCE:
 - DURABILITY: 60 Cycles and NoDamage
 - 5. Product No:
 - NC14-S 67 R * * - **
- CKTS
- CONNECTOR TYPE
- R:SMT H=4.00
- PLATING
- I:Gold flash
 - M:Au 5u"
 - R:Au 10u" Min
 - S:Au 15u"
- PACKING
- A:Tape&Reel
 - C:Tube
- REMARKS
- HF:Halogen free
 - Housing Black

Date code:
XXXX XX XX





Day (01,02...)

Month (01,02...)

Year (2024,2025...)

CUSTOMER DRAWING		东莞市文章济美电子有限公司		
Tolerance Unspecified (未注公差)	Size(图幅):	Product Name(产品名称):		
	Unit(单位):	0.5Pitch H=4.00 M.2 CARD CONNECTOR B KEY 4.0H G40.5A TYPE		
	Scale(比例):	Product No(产品料号):		
Project View (投影视图)		5001-C14-S67RRA-HF		
Rev 版本		Designer(设计):	Checked(审核):	Approved(核准):
Original Issue		吴小光		
Change Description 变更内容				
Date 日期				
Revisor 制/修订人				

Assembly stack height schematic diagram



HOW TO MATE AND EXTRACT

MATE: ① → ④

EXTRACT: ⑤ → ⑥

NOTE:Mating force will generate from step 3 to step 4.

CUSTOMER DRAWING

Tolerance Unspecified (未注公差)	Size(图幅):
0.0 ±0.25 0° ±5°	Unit(单位):
0.00 ±0.15 0°0 ±3°	MM
0.000 ±0.10 0°00 ±1°	Scale(比例):
	1:1
Project View (投影视角)	Page(页数):
	2 OF 3
	Rev(版本):
	A

东莞市文章济美电子有限公司

Product Name(产品名称):
0.5Pitch H=4.00 M.2 CARD CONNECTOR B KEY 4.0H G40.5A TYPEProduct No(产品料号):
5001-C14-S67RRA-HFDesigner(设计):
吴小光

Checked(审核):

Approved(核准):

A	Original Issue	2024/05/23	吴小光
Rev	Change Description	Date	Revisor
版本	变更内容	日期	制/修订人