



RHBS802 THRU RHBS810

Glass Passivated Single-Phase 8.0Amp Surface Mount Bridge Rectifier

Features

- Surface mount bridge, small package;
- Ideal for printed circuit boards;
- Glass passivated chip junction;
- High forward current capability up to 8.0A;
- High surge current capability;
- High heat dissipation capability;
- Low profile package;
- Low forward voltage drop;
- Plastic package has Underwriters Laboratory Flammability Classification 94V-0;


Mechanical Data

- Case: HBS;
- Epoxy meets UL-94V-0 Flammability rating;
- Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD22-B102;
- High temperature soldering guaranteed:
Solder Reflow 260°C, 10seconds;
- Polarity: As marked on body;
- Marking: Type number;

Typical Applications

General purpose use in AC-to-DC bridge full wave rectification for Fast Charging, Switching Power Supply, USB PD, Adapter and 3-in-1 Power Board, etc.

Case: HBS



Dimensions in inches and

Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified. Single Phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Parameter	Symbol	RHBS802	RHBS804	RHBS806	RHBS808	RHBS810	Unit
Maximum repetitive peak reverse voltage	V_{RRM}	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	200	400	600	800	1000	V
Maximum average forward rectified output current at $T_A=25^{\circ}\text{C}$	$I_{F(AV)}$	8.0					Amps
Non-Repetitive Peak forward surge current 8.3 ms single sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	200					Amps
Rating for fusing ($t < 8.3\text{ms}$)	I^2t	166					A^2sec
Instantaneous forward voltage drop per diode @ $I_F=1.0\text{A}$ @ $I_F=4.0\text{A}$ @ $I_F=8.0\text{A}$	V_F	0.95 1.1 1.3					Volt
Reverse Current at Rated DC Blocking Voltage $T_A=25^{\circ}\text{C}$ $T_A=125^{\circ}\text{C}$	I_R	0.20Typ. 50 Typ. 5.0 max 100 max.					μA
Maximum reverse recovery time ($I_F=0.5\text{A}, I_R=1.0\text{A}, I_{rr}=0.25\text{A}$)	T_{rr}	150	250	500			nS
Typical thermal resistance	$R_{\theta J-A}$ $R_{\theta J-C}$ $R_{\theta J-L}$	70.0 15.0 22.0					$^{\circ}\text{C/W}$
Operating junction and Storage Temperature Range	T_J, T_{STG}	-55 to +150					$^{\circ}\text{C}$






Note1: Measured at 1.0MHz and applied reverse voltage of 5.0V DC;



RHBS802 THRU RHBS810

Glass Passivated Single-Phase 8.0Amp Surface Mount Bridge Rectifier

Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted)



Suggested PCB printfoot layout

