






E		F		G	
Product NO. DOSIN-806-0229					
REV	DESCRIPTION	DWN	DATE	APPROVEN	
A	First issue	Mr. CHEN	2016/10/11	John kine	
B					



Specifications

Impedance:50 Ohms

Frequency Range:DC~3G

VSWR:1.3MAX

Working Voltage:500V rms @ sea level

Insulation Resistance:5000 Ohms min

Temperature Range:-65°C 10 +165°C

Relative Temperature:≤95%(40° C±2° C)

Drawings products are in line with ROHS standards

SIDE VIEW

BACK VIEW

RECOMMENDED FOOTPRINT

1		Body	Brass	NICKEL	NOTE:	Tolerance	X. X. X X. XX Angular ±0.15 ±0.10 ±0.05 ±5°
2		Insulator	TEFLON	White			
3		CONTACT PIN	BRASS	GOLD			
4							
5					DRAWN		
6					ZelIn. CHEN		
7					CHECKED	UNIT	MM
8							
9							
10					APPROVALS		
NO		Component Number	Material	Finish		SCALE	1:1
A			B		C	D	E
							</