





IMPEDANCE: 50 ohms
FREQUENCY RANGE: 0~6GHz
VSWR:1.5MAX
WITHSTANDING VOLTAGE:500V RMS@SEA LEVEL
INSULATION RESISTANCE: 5000 megohms min
TEMPERATURE RANGE: -65°C TO +165°C
RELATIVE TEMPERATURE:≤95%(40°C±2°C)

1	BODY	BRASS	Au: 3u"	1	NOTE: TOLERANCE UNLESS OTHERWISE SPECIFIED TOLERANCES FOR DIMENSIONS ARE 0.5-8MM±0.020MM 8-30MM±0.40MM 30-120MM±0.50MM	 	NAME: RP SMA JACK FOR PCB	DOSIN DOSIN INDUSTRIAL(HK)CO.,LTD 东莞市德索五金电子有限公司 Dongguan Dosin Hardware Electronics Co.,Ltd. Tel: (0086)769-81153906 Fax: (0086)769-81875836
2	INSULATOR	TEFLON	WHITE	1				
3	CONTACT PIN	BRASS	Au: 3u"	1				
4	NUIT	BRASS	Au: 3u"	1				
5	WASHER	BRASS	Au: 3u"	1				
6					DRAWN	2020/07/03		
7					W.cheng			
8					CHECKED			
9							UNIT	MM
10					APPROVALS		SCALE	1 : 1
NO	COMPONENT NUMBER	MATERIAL	FINISH	QTY				
A		B		C		D		E
						F		G