





PRODUCT NO:		DS806FCS0002		
REV	DESCRIPTION	DWN	DATE	APPROVEN
A	FIRST ISSUE	W.cheng	2019/10/25	John kine
B				



SPECIFICATIONS:

IMPEDANCE: 50 ohms
FREQUENCY RANGE: 0~6GHZ
VSWR: 1.5MAX
WORKING VOLTAGE: 500V RMS@SEA LEVL
INSULATION RESISTANCE: 5000 ohms min
TEMPERATURE RANGE: -65°C TO +165°C
RELATIVE TEMPERATURE: < 95%(40°C±2°C)

1	BODY	BRASS	GOLD	1	NOTE:	TOLERANCE	UNLESS OTHERWISE SPECIFIED TOLERANCES: FDRINCHES ARE 0.5-8MM±0.020MM 8-30MM±0.40MM 30-120MM±0.50MM	DONGGUAN DOSIN INDUSTRIAL(HK)CO.,LTD Dongguan Dosin Hardware Electronics Co.,Ltd. Fax: (0086)769-81875836	
2	INSULATOR	TEFLON	WHITE	1					
3	CONTACT PIN	BRASS	GOLD	1					
4					DRAWN	2019/10/25		NAME: SMA JACK CONNECTOR	
5									
6									
7					CHECKED		MM	SIZE A	
8									
9								PRODUCT NO: DS806FCS0002	
10					APPROVALS			DATE TIME 2019/10/25	
NO	COMPONENT NUMBER	MATERIAL	FINISH	QTY			SCALE 1 : 1	CAD FILE H/compandrawings/BD	SHEET: 1 OF 1
A		B		C		D		E	
								F	
								G	