




Code-x	H	Code-x	H
A	4.30	O	11.00
B	4.50	P	11.50
C	5.00	Q	12.00
D	5.50	R	12.50
E	6.00	S	13.00
F	6.50	T	13.50
G	7.00	U	14.00
H	7.50	V	15.00
I	8.00	W	15.50
J	8.50	X	16.00
K	9.00	Y	16.50
L	9.50	Z	17.00
M	10.00	18	18.00
N	10.50	19	19.00



Technical drawing of a stepped shaft. The shaft has a total length of 21.00 [0.027] and a diameter of 17.00 [0.669]. The drawing shows a stepped profile with a central vertical axis and a horizontal centerline. The dimensions are indicated by arrows and text labels.

Contact Rating: 50mA, 12V DC
Contact Resistance: 100m Ω max
Insulation Resistance: 100M Ω min. 500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.25mm
Operating Temp: -40 $^{\circ}$ C~+80 $^{\circ}$ C
Storage Temp: -40 $^{\circ}$ C~+80 $^{\circ}$ C

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	

XK13 星城 Connection

DESIGN	阿树	VIEW:		MODEL TYPE:	TACT SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	TS-1102SD-A-D-R
APPROVED		SIZE:	A4	DWG NO.:	TS-1102SD-A-D-R
PRECISION CO., LIMITED				SCALE	PAGE
				N/A	1/1
				REVISION	
				A1	