




Voltage rating: 600V AC / DC
Current rating: 23A AC / DC
Withstanding voltage: 2200V AC/minute
Temperature range: -40°C~+105°C
Insulation resistance: $\geq 1000M\Omega$
Contact resistance: $\leq 2m\Omega$
After environmental testing: $\leq 10m\Omega$
Plug the Pin & Special No.: H-High conductive Brass

① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : V-Straight 180°
- ④ Row No.-Pin No. : 2xXX-2x02P~2x06P
- ⑤ Material: LP -LCP 94V-0
- ⑥ Plating Category: SW-Matte Tin Plating



Poles	Dimensions (mm)		
	AB		C
2x01	8.35		12.34
2x02	12.05	5.70	16.04
2x03	17.75	11.40	21.74
2x04	23.45	17.10	27.44
2x05	29.15	22.80	33.14
2x06	34.85	28.50	38.84



X5700WV-2x01-LPSW	High conductive Brass	X5700H	X5700T
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

							DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector		
Δx					units:	mm	DWN		DATE		VIEW: 	PART NO.: X5700WV-2x01-LPSW		
Δx					tolerance:		CHKD		DATE		UNIT: mm/in	DWG NO.: X-X5700WV-2x01-LPSW		
Δx						X.X $\pm 0.2\text{mm}$	APPD		DATE		SIZE: A4			
Δx						X.XX $\pm 0.1\text{mm}$								
MARK	DESCRIPTION				DATE	REVISED	APPROVED							
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												WEIGHT 1.0g	*SHEET 1/1	REVISION A0