

规格 SPECIFICATIONS:

- 1. 电气特性 ELECTRICAL CHARACTERISTICS:
 - 1-1. 额定电流 CURRENT RATING: 1A
 - 1-2. 接触电阻 CONTACT RESISTANCE:
 - 1-2-1. 100mΩ MAX. (INITIAL) (FOR C1/C2/C3/C4/C5/C6/C7/C8)
 - 1-2-2. 500mΩ MAX. (INITIAL) (FOR CD/COMMON)
 - 1-3. 绝缘耐压 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR ONE MINUTE.
 - 1-4. 绝缘电阻 INSULATION RESISTANCE: 100MΩ MIN. BY 500V DC.
- 2. 机械特性 MECHANICAL CHARACTERISTICS:
 - 2-1. 寿命测试 LIFE TEST: 5000 CYCLES MIN.
- 3. 环境特性 ENVIRONMENTAL CHARACTERISTICS:
 - 3-1. 盐雾试验 SALT MIST TEST CONDITION: PER IEC 68-2-52, SEVERITY(3)
 - 3-2. 工作温度 OPERATING TEMPERATURE: -30°~+80°
 - 3-3. TO CONFORM TO SINGATRON HAZARDOUS SUBSTANCE FREE SPEC.
 - 3-4. RoHS COMPLIANT PRODUCT.
 - 3-5. HALOGEN FREE PRODUCT IDENTIFICATION MARK:
 - 3-6. HALOGEN FREE PRODUCT IDENTIFICATION LABEL ON PACKAGING:

F	LINK	1	STAINLESS STEEL T=0.10	N/A
E	SPRING	1	SWP	NICKEL PLATING
D	SLIDE	1	HIGH TEMP.THERMOPLASTIC, UL94V-0 AND STAINLESS STEEL	BLACK
C	SHELL	1	SUS 301 1/2H T=0.1	NICKEL PLATING
B	CONTACT	1	C5210 EH T=0.10 45M2019-002002	3U" GOLD PLATING ONCONTACT AREA AND SOLDER AREA,50U" MIN NICKEL UNDER PLATING
A	HOUSING	1	LCP+35%GF S475 UL94V-0	BLACK

XK13 星城
Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED