




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.11.14	阿树

A



SECT B-B






U261-24XN-4BS65-PC-1P

- 1: Au1u"
- 2: Au3u"
- 4: Au15u"
- 5: Au30u"



C TYPE PLUG:		PCB:
A1+A12+B1+B12	——	GND
A4+A9+B4+B9	——	VCC
A5	——	A5(CC1)
A6+B6	——	A6+B6(D+)
A7+B7	——	A7+B7(D-)
A8	——	A8(SBU1)
B5	——	B5(CC2)
B8	——	B8(SBU2)

B




- REMARKS:
- CONTACT INSERTION AND WITHDRAW FORCE:
 - 1.Insertion force: 5N~20N max.
 - 2. Withdrawal force: 8N~20N.
 - 3.Durability : 10000Cycles.
 - ELECTRIC PROPERTY:
 - 1.Contact current rating: 3A.
 - 2.Dielectric Strength: 100V AC(RMS).
 - 3.Insulation Resistance: 100 megaohms min.
 - 4.Contact resistance:
 - 40mOhms MAX.FOR VBUS,GND AND OTHER CONTACT
 - 50mOhms MAX.AFTER ENVIRONMENT TEST
 - AMBIENT TEMPERATURE:
 - 1.Operating temperature: -55°C to +85°C.

C



SECT A-A




D
2:1

6	Shrapnel	SUS T=0.10mm	
5	Shell	SUS T=0.15mm	Ovep-plating: Ni
4	Terminal	C7025 T=0.15mm	Ovep-plating: Au Ni/Sn
3	Latch	SUS T=0.4mm	
2	Housing	LCP	UL94-0
1	Housing Stopper	LCP	UL94-0
ITEM	DESCRIPTION	MATERIAL	REMARKS

A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1
GND	RX2+	RX2-	Vbus	SBU1	D-	D+	CC	Vbus	TX1-	TX1+	GND
GND	TX2+	TX2-	Vbus	Vconn			SBU2	Vbus	RX1-	RX1+	GND
B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12

D

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: USB TYPE C-24PIN PLUG
CHECKED		UNIT: mm/in	PART NO.: U261-24XN-4BS65-PC-1P
APPROVED		SIZE: A4	DWG NO.: