

Specifications:

规格:

Voltage rating:125V AC/DC

额定电压: 125V AC/DC

Current rating:2A AC/DC

额定电流: 2A AC/DC

Contact Resistance:≤20MΩ

接触电阻: ≤20MΩ

Insulation Resistance:≥500MΩ

绝缘电阻:≥500MΩ





Dielectric strength:800V AC/minutenai

耐压: 800V AC/minute

X1506W R S -16-9T SW

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
- ② Category:W-WAFER
- ③ Welding Board Angle:R-90°
- ④ Welding Way:S-SMT
- ⑤ Row No-Pin No:XX-02-16PIN
- ⑥ Material:9T-PA9T 94V-0
- ⑦ Plating Category:SW-Matte Tin Plating(Tin:70u Min)



Recommended P.C.B Layout
General Tolerance±0.05

Poles	Dimensions(mm)		
	A	B	C
2	6.25	1.50	3.75
3	7.75	3.00	5.25
4	9.25	4.50	6.75
5	10.75	6.00	8.25
6	12.25	7.50	9.75
7	13.75	9.00	11.25
8	15.25	10.50	12.75
9	16.75	12.00	14.25
10	18.25	13.50	15.75
11	19.75	15.00	17.25
12	21.25	16.50	18.75
13	22.75	18.00	20.25
14	24.25	19.50	21.75
15	25.75	21.00	23.25
16	27.25	22.50	24.75

X1506WRS-16-9TSW	PA9T UL 94V-0	Brass	Tin -Pated	X1506T
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

ΔX					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
DESCRIPTION					DATE	REVISED
REVISIONS					APPROVED	UNSPECIFIED TOLERANCES



DSND		SCALE: N/A	MODEL TYPE: 1.50mm Crimp Style Connectors
DWN		VIEW:	PART NO.: X1506WRS-16-9TSW
CHKD		UNIT: mm/in	DWG NO.: X-X1506WRS-16-9TSW
APPD		SIZE: A4	WEIGHT
			SHEET
			REVISION
			1/1
			A0