





Technical drawing of a mechanical part showing a cross-section. The drawing includes the following dimensions and features:

- Overall width: $B \pm 0.30$
- Distance between the first and second pins: $2.50 [0.098]$
- Distance between the last two pins: $A \pm 0.20$
- Pin diameter: $\varnothing 0.60 [0.024]$
- Pin length: 2.50 ± 0.10
- Top surface features: A central rectangular feature and two side features with rounded corners.
- Bottom surface features: A series of pins and a central rectangular feature.



接触电阻: 20mΩ Max

X2508 W V - 2x09 A - N0 SN
 (1) (2) (3) (4) (5) (6) (7)

1.Series No
2.Category:W-Wafer
3.Welding Board Range:V-Stright 180°
4.Row No.Pin No:2xXX-2x02~2x20 Pin
5.Special No.
6.Material:N0-Nylon 66 UL94V-0
7.Plating:SN-Plated Tin

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2x02	2.50	10.00	6.40	2x10	22.50	30.00	26.40
2x03	5.00	12.50	8.90	2x11	25.00	32.50	28.90
2x04	7.50	15.00	11.40	2x12	27.50	35.00	31.40
2x05	10.00	17.50	13.90	2x13	30.00	37.50	33.90
2x06	12.50	20.00	16.40	2x14	32.50	40.00	36.40
2x07	15.00	22.50	18.90	2x15	35.00	42.50	38.90
2x08	17.50	25.00	21.40	...	...	...	...
2x09	20.00	27.50	23.90	2x20	47.50	55.00	51.40

X2508WV-2x09A-N0SN	Nylon 66	Brass	X2508H-A
PART NO	Material	Material(Pin)	Suitable XKE Housing

SCALE: N/A		MODEL TYPE: 2.5mm Crimp Style Connector	
DSND DWN	VIEW: 	PART NO.: X2508WV-2x09A-N0SN	
CHKD	UNIT: mm/in	DWG NO.: X-X2508WV-2x09A-N0SN	
APPD	SIZE: A4		
L PRECISION CO.,LIMITED		WEIGHT	SHEET 1/1
			REVISION A0

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxb.com www.helloxb.cn www.xk-da.cn						

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED