


Recommended P.C.B
Layout(±0.05)



Technical Data
Pin(outer sleeve):Brass,machined CuZn38Pb2
Cllp(Contact 6 Finger):Beryllium copper,heat teated
Insulator:PPS UL94V-0 colour:black
Current rating:3Amps
Mating pin Ø:0.635/0.889mm
Forces:(polished steel gaugeØ0.66mm)
-Insertion:1.2N typ
-Withdrawal:0.6N typ
Mechanical life:min 500cycles
Contact resistance:max 10m Ω
Dielectric strength:min 1000V RMS
Operating temperature:-40°C to+105°C
Soldering temperature:+255°C

X5521 F V-2x13-C70 D30-1000

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series.N0.
- ② Category : F-Female
- ③ Welding Board Angle : V-Straight 180°
- ④ Row No-Pin No:2*XX-01P-XXP
- ⑤ Plastic Height :C=7.0mm
- ⑥ Pin Length :D=3.0mm
- ⑦ 1000:TYPE 1000

X5521FV-2x13-C70D30-1000	PPS 94V-0	Brass	Tin Gold 1u"	X5521FV
PART N0	Material	Material(Terminal)	Finish(Terminal)	Mates With XKB Pin Header

						DSND		DATE		SCALE: N/A	MODEL TYPE:
Δx					ANGLAR	DWN		DATE		VIEW:	PART NO.:
Δx					L ≤ 4	CHKD		DATE		UNIT: mm/in	
Δx					4 < L ≤ 16	APPD		DATE		SIZE: A4	DWG NO.:
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	XKB INDUSTRIAL PRECISION CO.,LIMITED					
					L > 63						
					UNSPECIFIED TOLERANCES						
REVISIONS											
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											
										WEIGHT	SHEET
										1.0g	1/1
										REVISION	
										A0	