




序号	品名	材质
1	0.5 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0 颜色:黑色
2	0.5 Pitch双槽立式BTB母座端子	铜合金/表面点镀金
3	0.5 Pitch双槽立式BTB母座吸盖	LCP UL94 V-0 颜色:黑色.

PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
BTB0.5-MH2.2-8PALTI	8	1.50	2.55	4.70	3.40	4.00
BTB0.5-MH2.2-10PALTI	10	2.00	3.05	5.20	3.90	
BTB0.5-MH2.2-12PALTI	12	2.50	3.55	5.70	4.40	
BTB0.5-MH2.2-14PALTI	14	3.00	4.05	6.20	4.90	
BTB0.5-MH2.2-16PALTI	16	3.50	4.55	6.70	5.40	
BTB0.5-MH2.2-18PALTI	18	4.00	5.05	7.20	5.90	
BTB0.5-MH2.2-20PALTI	20	4.50	5.55	7.70	6.40	
BTB0.5-MH2.2-22PALTI	22	5.00	6.05	8.20	6.90	
BTB0.5-MH2.2-24PALTI	24	5.50	6.55	8.70	7.40	
BTB0.5-MH2.2-26PALTI	26	6.00	7.05	9.20	7.90	
BTB0.5-MH2.2-28PALTI	28	6.50	7.55	9.70	8.40	
BTB0.5-MH2.2-30PALTI	30	7.00	8.05	10.20	8.90	
BTB0.5-MH2.2-32PALTI	32	7.50	8.55	10.70	9.40	
BTB0.5-MH2.2-34PALTI	34	8.00	9.05	11.20	9.90	
BTB0.5-MH2.2-36PALTI	36	8.50	9.55	11.70	10.40	
BTB0.5-MH2.2-38PALTI	38	9.00	10.05	12.20	10.90	8.00
BTB0.5-MH2.2-40PALTI	40	9.50	10.55	12.70	11.40	
BTB0.5-MH2.2-44PALTI	44	10.50	11.05	13.70	12.40	
BTB0.5-MH2.2-50PALTI	50	12.00	13.05	15.20	13.90	
BTB0.5-MH2.2-60PALTI	60	14.50	15.55	17.70	16.40	
BTB0.5-MH2.2-70PALTI	70	17.00	18.05	20.20	18.90	
BTB0.5-MH2.2-80PALTI	80	19.50	20.55	22.70	21.40	
BTB0.5-MH2.2-100PALTI	100	24.50	25.55	27.70	26.40	

High photosynthesis 合高 (H)	The female seat neight 母座单高 (H1)	The male seat neight 公座单高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围:-40° C~85° C.
3. 额定电压:50V, AC.
4. 接触电阻:≤0.02 Ω.
5. 绝缘电阻:≥100M Ω

适用线路板

GENERAL TOLERANCES UNLESS SPECIFIED		深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd	
X.±0.50	±1°	PART NO.	TITLE:
.X±0.20		BTB0.5-MH2.2-NPALTI	0.5 Pitch双槽立式BTB母(单高2.2)
.XX±0.10		DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE
		APPD: Sophia	UNITS
			A4
			SCALE
			N:A
			SHEET
			1/1