

Features

- Ultra low leakage: nA level
- Low operating voltage: 15V
- Low clamping voltage
- 2-pin leadless package
- Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test
Air discharge: $\pm 30\text{kV}$
Contact discharge: $\pm 30\text{kV}$
 - IEC61000-4-5 (Lightning) 5A (8/20 μs)
- RoHS Compliant


Applications

- Cell Phone Handsets and Accessories
- Microprocessor based equipment
- Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers
- Portable Instrumentation
- Networking and Telecom
- Serial and Parallel Ports
- Peripherals


Mechanical Characteristics

- Package: DFN0603
- UL Flammability Classification Rating 94V-0
- Quantity Per Reel: 10,000 pcs
- Reel Size: 7 inch
- Device Marking: K

Dimensions DFN0603



Pin Configuration



Absolute Maximum Ratings (T_{amb}=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20 μs)	P _{pp}	130	W
ESD per IEC 61000-4-2 (Air)	V _{ESD}	± 30	kV
ESD per IEC 61000-4-2 (Contact)		± 30	
Operating Temperature Range	T _J	-55 to +125	°C
Storage Temperature Range	T _{STJ}	-55 to +150	°C

Electrical Characteristics (TA=25°C unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				15	V
Breakdown Voltage	V_{BR}	$I_T = 1\text{mA}$	16.7		22	V
Reverse Leakage Current	I_R	$V_{RWM} = 15\text{V}$			0.5	μA
Clamping Voltage	V_C	$I_{PP} = 5\text{A}$ (8 x 20 μs pulse)			26	V
Junction Capacitance	C_J	$V_R = 0\text{V}$, $f = 1\text{MHz}$		5	6.5	pF

Electrical Parameters (TA=25°C unless otherwise specified)

V_{RWM} Reverse Working Voltage Max.


I_R Maximum Reverse Leakage Current @ V_{RWM}

I_T Test Current

V_{BR} Reverse Breakdown Voltage

I_{PP} Maximum Reverse Peak Pulse Current

V_C Clamping Voltage @ I_{PP}



Typical Performance Characteristics (TA=25°C unless otherwise specified)

Figure1: 8/20μs pulse waveform according to IEC61000-4-5




Figure2: ESD pulse waveform according to IEC 61000-4-2




Figure3: Power Derating Curve






Figure 4: Clamping Voltage vs. I_{pp}




DFN0603 Package Outline Drawing



COMMON DIMENSION (mm)			
PKG	DFN0603		
REF.	MIN.	NOM.	MAX.
A	0.28	0.30	0.34
A1	0.00	0.02	0.05
b	0.14		0.24
L	0.21	0.23	0.265
e	0.40BSC		
D	0.25	0.30	0.35
E	0.55	0.60	0.65

Suggested Land Pattern



* This land pattern is for reference purposes only

NOTICE

Leiditech reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Leiditech does not assume any liability arising out of the application or use of any product described herein.

Shanghai Leiditech Electronic Technology Co., Ltd.

Email: sale1@leiditech.com

Tel : +86- 021 50828806

Fax : +86- 021 50477059