



Specifications:

规格:

Voltage rating:100V AC/DC

额定电压: 100V AC/DC

Current rating:0.3A AC/DC

额定电流: 0.3A AC/DC

Withstanding voltage:150V AC/minute

耐受电压: 150V AC/分钟

Temperature range:-40°C-+125°C

温度范围: -40℃-+125℃

Insulation resistance:100MΩ min

绝缘电阻: 100MΩ Min

Contact resistance:50mΩ Max

接触电阻: 50mΩ Max

X0502 F V S - 10 C S - LP SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

- 1.Series No
- 2.Category:F-Female
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-10~80P
- 6.Height:A:2.2mm; B:2.3mm; C:2.9mm;
- 7.Type :Blank-There are no side two ground tags
1-There are with side two ground tags
- 8.Special No:S-With positioning column
- 9.Material:LP-LCP UL94V-0
- 10.Plating:SN-Tin Plated or V01-Gold Flash

Mating Height	PLUG	SOCKET
3.0	2.1	2.2
3.4	2.2	2.3
4.0	2.2	2.9
5.0	2.7	4.3

Poles	Dimensions(mm)				Poles	Dimensions(mm)			
	A	B	C	D		A	B	C	D
10	4.70	2.00	3.20	4.10	32	10.20	7.50	8.70	9.60
12	5.20	2.50	3.70	4.60	36	11.20	8.50	9.70	10.60
14	5.70	3.00	4.20	5.10	40	12.20	9.50	10.70	11.60
20	7.20	4.50	5.70	6.60	50	14.70	12.00	13.20	14.60
22	7.70	5.00	6.20	7.10	60	17.20	14.50	15.70	16.60
24	8.20	5.50	6.70	7.60	80	22.20	19.50	20.70	21.60
30	9.70	7.00	8.20	9.10		/			

X0502FVS-10CS-LPSN	LCP	Copper Alloy	X0502FVS
PART NO	Material	Material(Pin)	Suitable XKB Wafer

DSND		SCALE: N/A	MODEL TYPE: 0.5mm BTB Connector
DWN		VIEW: 	PART NO.: X0502FVS-10CS-LPSN
CHKD		UNIT: mm/in	DWG NO.: X-X0502FVS-10CS-LPSN
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0

					ANGLAR	±5°
△X					L≤ 4	±0.2
△X					4<L≤ 16	±0.3
△X					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED