


A



DS037-00P-60



Specifications:

规格:

额定电压, 电流 Rated voltage and current: DC30V 0.1A

使用温度范围Operating temperature range: $-25^{\circ}\text{C} \sim +65^{\circ}\text{C}$

电气寿命Electric lifetime:5E4 cycles

动作力Operating force:30±20gf

接触电阻 Contact Resistance: $\leq 1\Omega$

耐压(Withstand Voltage): AC250V

绝缘电阻(Insulation Resistance): $\geq 50\text{M}\Omega$ (Test Voltage DC500V)

7	Handle	1	PA66	Black
6	Electric shock	1	Ag	
5	Reeds	1	Beryllium bronze	
4	Button	1	PA66	white
3	Lugs	1	Brass	Ag-Plated
2	Cover	1	PA66	Black
1	Pedestal	1	PA66	Black
NO	NAME	QTY	MATERIAL	Remark

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW: 	MODEL TYPE: MICRO SWITCH		
CHECKED		UNIT: mm/in	PART NO.: DS037-00P-60		
APPROVED		SIZE: A4	DWG NO.: X-DS037-00P-60		
TECHNICAL CO., LIMITED			SCALE	PAGE	REVISION

www.xk-dq.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED