



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.09	阿树



- SPECIFICATIONS
- Voltage rating:125V AC/DC
 - Current rating:3A AC/DC
 - Withstanding Voltage:1000V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤10mΩ
 - After environmental testing:≤20mΩ

PART NO.:
X2004 W V-03-N0 SN
① ② ③ ④ ⑤ ⑥

①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Row No.Pin No:XX-02~16Pin
⑤Material: N0-PA66 UL94V-0
⑥Planting:SN-Tin Plated



02P~03P Single Gap
Scale 1:1

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	




XKB INDUSTRIAL PRECISION CO.,LIMITED

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	5.96	4.96	10	18.00	21.96	20.96
03	4.00	7.96	6.96	11	20.00	23.96	22.96
04	6.00	9.96	8.96	12	22.00	25.96	24.96
05	8.00	11.96	10.96	13	24.00	27.96	26.96
06	10.00	13.96	12.96	14	26.00	29.96	28.96
07	12.00	15.96	14.96	15	28.00	31.96	30.96
08	14.00	17.96	16.96	16	30.00	33.96	32.96
09	16.00	19.96	18.96				

X2004WV-03SHF-9TSN	PA9T UL 94V-0 (Halogen Free)	Brass	Tin-Plated	X2004H
X2004WV-03-N0SN	PA66 UL 94V-0			
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Terminal

DESIGN	阿树	VIEW:		MODEL TYPE: 2.00mm Crimp Style Connectors		
CHECKED		UNIT:	mm/in	PART NO.: X2004WV-03-N0SN		
APPROVED		SIZE:	A4	DWG NO.: X-X2004WV-03-N0SN		
PRECISION CO.,LIMITED				SCALE	PAGE	REVISION
				N/A	1/1	A1



02P~15P Double Gap
Scale 1:1

Recommended P.C.B Layout
General Tolerance±0.05