




1				2				3				4																																																																																																																																																																																																													
A									REVISIONS																																																																																																																																																																																																																
									REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN																																																																																																																																																																																																											
									A0	N/A		INITIAL RELEASE	/	/																																																																																																																																																																																																											
									A1	N/A		图面升级整理图面	2025.05.20	阿树																																																																																																																																																																																																											
B	<table><tr><td>Poles</td><td>DIM A</td><td>DIM B</td><td>DIM C</td><td>Poles</td><td>DIM A</td><td>DIM B</td><td>DIM C</td><td>Poles</td><td>DIM A</td><td>DIM B</td><td>DIM C</td></tr><tr><td>5</td><td>2.00</td><td>7.50</td><td>4.40</td><td>21</td><td>10.00</td><td>15.50</td><td>12.40</td><td>37</td><td>18.00</td><td>23.50</td><td>20.40</td></tr><tr><td>6</td><td>2.50</td><td>8.00</td><td>4.90</td><td>22</td><td>10.50</td><td>16.00</td><td>12.90</td><td>38</td><td>18.50</td><td>24.00</td><td>20.90</td></tr><tr><td>7</td><td>3.00</td><td>8.50</td><td>5.40</td><td>23</td><td>11.00</td><td>16.50</td><td>13.40</td><td>39</td><td>19.00</td><td>24.50</td><td>21.40</td></tr><tr><td>8</td><td>3.50</td><td>9.00</td><td>5.90</td><td>24</td><td>11.50</td><td>17.00</td><td>13.90</td><td>40</td><td>19.50</td><td>25.00</td><td>21.90</td></tr><tr><td>9</td><td>4.00</td><td>9.50</td><td>6.40</td><td>25</td><td>12.00</td><td>17.50</td><td>14.40</td><td>41</td><td>20.00</td><td>25.50</td><td>22.40</td></tr><tr><td>10</td><td>4.50</td><td>10.00</td><td>6.90</td><td>26</td><td>12.50</td><td>18.00</td><td>14.90</td><td>42</td><td>20.50</td><td>26.00</td><td>22.90</td></tr><tr><td>11</td><td>5.00</td><td>10.50</td><td>7.40</td><td>27</td><td>13.00</td><td>18.50</td><td>15.40</td><td>43</td><td>21.00</td><td>26.50</td><td>23.40</td></tr><tr><td>12</td><td>5.50</td><td>11.00</td><td>7.90</td><td>28</td><td>13.50</td><td>19.00</td><td>15.90</td><td>44</td><td>21.50</td><td>27.00</td><td>23.90</td></tr><tr><td>13</td><td>6.00</td><td>11.50</td><td>8.40</td><td>29</td><td>14.00</td><td>19.50</td><td>16.40</td><td>45</td><td>22.00</td><td>27.50</td><td>24.40</td></tr><tr><td>14</td><td>6.50</td><td>12.00</td><td>8.90</td><td>30</td><td>14.50</td><td>20.00</td><td>16.90</td><td>46</td><td>22.50</td><td>28.00</td><td>24.90</td></tr><tr><td>15</td><td>7.00</td><td>12.50</td><td>9.40</td><td>31</td><td>15.00</td><td>20.50</td><td>17.40</td><td>47</td><td>23.00</td><td>28.50</td><td>25.40</td></tr><tr><td>16</td><td>7.50</td><td>13.00</td><td>9.90</td><td>32</td><td>15.50</td><td>21.00</td><td>17.90</td><td>48</td><td>23.50</td><td>29.00</td><td>25.90</td></tr><tr><td>17</td><td>8.00</td><td>13.50</td><td>10.40</td><td>33</td><td>16.00</td><td>21.50</td><td>18.40</td><td>49</td><td>24.00</td><td>29.50</td><td>26.40</td></tr><tr><td>18</td><td>8.50</td><td>14.00</td><td>10.90</td><td>34</td><td>16.50</td><td>22.00</td><td>18.90</td><td>50</td><td>24.50</td><td>30.00</td><td>26.90</td></tr><tr><td>19</td><td>9.00</td><td>14.50</td><td>11.40</td><td>35</td><td>17.00</td><td>22.50</td><td>19.40</td><td>51</td><td>25.00</td><td>30.50</td><td>27.40</td></tr><tr><td>20</td><td>9.50</td><td>15.00</td><td>11.90</td><td>36</td><td>17.50</td><td>23.00</td><td>19.90</td><td>0</td><td>0.00</td><td>0.00</td><td>0.00</td></tr></table>												Poles	DIM A	DIM B	DIM C	Poles	DIM A	DIM B	DIM C	Poles	DIM A	DIM B	DIM C	5	2.00	7.50	4.40	21	10.00	15.50	12.40	37	18.00	23.50	20.40	6	2.50	8.00	4.90	22	10.50	16.00	12.90	38	18.50	24.00	20.90	7	3.00	8.50	5.40	23	11.00	16.50	13.40	39	19.00	24.50	21.40	8	3.50	9.00	5.90	24	11.50	17.00	13.90	40	19.50	25.00	21.90	9	4.00	9.50	6.40	25	12.00	17.50	14.40	41	20.00	25.50	22.40	10	4.50	10.00	6.90	26	12.50	18.00	14.90	42	20.50	26.00	22.90	11	5.00	10.50	7.40	27	13.00	18.50	15.40	43	21.00	26.50	23.40	12	5.50	11.00	7.90	28	13.50	19.00	15.90	44	21.50	27.00	23.90	13	6.00	11.50	8.40	29	14.00	19.50	16.40	45	22.00	27.50	24.40	14	6.50	12.00	8.90	30	14.50	20.00	16.90	46	22.50	28.00	24.90	15	7.00	12.50	9.40	31	15.00	20.50	17.40	47	23.00	28.50	25.40	16	7.50	13.00	9.90	32	15.50	21.00	17.90	48	23.50	29.00	25.90	17	8.00	13.50	10.40	33	16.00	21.50	18.40	49	24.00	29.50	26.40	18	8.50	14.00	10.90	34	16.50	22.00	18.90	50	24.50	30.00	26.90	19	9.00	14.50	11.40	35	17.00	22.50	19.40	51	25.00	30.50	27.40	20	9.50	15.00	11.90	36	17.50	23.00	19.90	0	0.00	0.00	0.00	C
	Poles	DIM A	DIM B	DIM C	Poles	DIM A	DIM B	DIM C	Poles	DIM A	DIM B	DIM C																																																																																																																																																																																																													
	5	2.00	7.50	4.40	21	10.00	15.50	12.40	37	18.00	23.50	20.40																																																																																																																																																																																																													
	6	2.50	8.00	4.90	22	10.50	16.00	12.90	38	18.50	24.00	20.90																																																																																																																																																																																																													
	7	3.00	8.50	5.40	23	11.00	16.50	13.40	39	19.00	24.50	21.40																																																																																																																																																																																																													
	8	3.50	9.00	5.90	24	11.50	17.00	13.90	40	19.50	25.00	21.90																																																																																																																																																																																																													
	9	4.00	9.50	6.40	25	12.00	17.50	14.40	41	20.00	25.50	22.40																																																																																																																																																																																																													
	10	4.50	10.00	6.90	26	12.50	18.00	14.90	42	20.50	26.00	22.90																																																																																																																																																																																																													
	11	5.00	10.50	7.40	27	13.00	18.50	15.40	43	21.00	26.50	23.40																																																																																																																																																																																																													
	12	5.50	11.00	7.90	28	13.50	19.00	15.90	44	21.50	27.00	23.90																																																																																																																																																																																																													
	13	6.00	11.50	8.40	29	14.00	19.50	16.40	45	22.00	27.50	24.40																																																																																																																																																																																																													
	14	6.50	12.00	8.90	30	14.50	20.00	16.90	46	22.50	28.00	24.90																																																																																																																																																																																																													
	15	7.00	12.50	9.40	31	15.00	20.50	17.40	47	23.00	28.50	25.40																																																																																																																																																																																																													
	16	7.50	13.00	9.90	32	15.50	21.00	17.90	48	23.50	29.00	25.90																																																																																																																																																																																																													
	17	8.00	13.50	10.40	33	16.00	21.50	18.40	49	24.00	29.50	26.40																																																																																																																																																																																																													
	18	8.50	14.00	10.90	34	16.50	22.00	18.90	50	24.50	30.00	26.90																																																																																																																																																																																																													
	19	9.00	14.50	11.40	35	17.00	22.50	19.40	51	25.00	30.50	27.40																																																																																																																																																																																																													
	20	9.50	15.00	11.90	36	17.50	23.00	19.90	0	0.00	0.00	0.00																																																																																																																																																																																																													
	D	<table><tr><td>AuGLAR</td><td>±5°</td></tr><tr><td>X.</td><td>±0.40</td></tr><tr><td>X.x</td><td>±0.30</td></tr><tr><td>X.xx</td><td>±0.20</td></tr><tr><td>X.xxx</td><td>±0.15</td></tr><tr><td colspan="2">UNSPECIFIED TOLERANCES</td></tr></table>				AuGLAR	±5°	X.	±0.40	X.x	±0.30	X.xx	±0.20	X.xxx	±0.15	UNSPECIFIED TOLERANCES				DESIGN	阿树	VIEW: 	MODEL TYPE: FPC CONNECTOR	D																																																																																																																																																																																																	
		AuGLAR	±5°																																																																																																																																																																																																																						
X.		±0.40																																																																																																																																																																																																																							
X.x		±0.30																																																																																																																																																																																																																							
X.xx	±0.20																																																																																																																																																																																																																								
X.xxx	±0.15																																																																																																																																																																																																																								
UNSPECIFIED TOLERANCES																																																																																																																																																																																																																									
		CHECKED		UNIT: mm/in	PART NO.: X05A21LKXXG																																																																																																																																																																																																																				
		APPROVED		SIZE: A4	DWG NO.:																																																																																																																																																																																																																				
XKB INDUSTRIAL PRECISION CO.,LIMITED												SCALE N/A	PAGE 2/2	REVISION A1																																																																																																																																																																																																											
1				2				3				4																																																																																																																																																																																																													