




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\ \Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\ \Omega$ 。

序号	品名	材质
①	0.5 Pitch B型单槽立式BTB母座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型单槽立式BTB母座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
BTB0.5-MH2.2-10PBLT1	2X5	2.00	3.20	4.70	4.10
BTB0.5-MH2.2-12PBLT1	2X6	2.50	3.70	5.20	4.60
BTB0.5-MH2.2-14PBLT1	2X7	3.00	4.20	5.70	5.10
BTB0.5-MH2.2-16PBLT1	2X8	3.50	4.70	6.20	5.60
BTB0.5-MH2.2-18PBLT1	2X9	4.00	5.20	6.70	6.10
BTB0.5-MH2.2-20PBLT1	2X10	4.50	5.70	7.20	6.60
BTB0.5-MH2.2-22PBLT1	2X11	5.00	6.20	7.70	7.10
BTB0.5-MH2.2-24PBLT1	2X12	5.50	6.70	8.20	7.60
BTB0.5-MH2.2-26PBLT1	2X13	6.00	7.20	8.70	8.10
BTB0.5-MH2.2-28PBLT1	2X14	6.50	7.70	9.20	8.60
BTB0.5-MH2.2-30PBLT1	2X15	7.00	8.20	9.70	9.10
BTB0.5-MH2.2-32PBLT1	2X16	7.50	8.70	10.20	9.60
BTB0.5-MH2.2-34PBLT1	2X17	8.00	9.20	10.70	10.10
BTB0.5-MH2.2-36PBLT1	2X18	8.50	9.70	11.20	10.60
BTB0.5-MH2.2-38PBLT1	2X19	9.00	10.20	11.70	11.10
BTB0.5-MH2.2-40PBLT1	2X20	9.50	10.70	12.20	11.60
BTB0.5-MH2.2-44PBLT1	2X22	10.50	11.70	13.20	12.60
BTB0.5-MH2.2-50PBLT1	2X25	12.00	13.20	14.70	14.10
BTB0.5-MH2.2-60PBLT1	2X30	14.50	15.70	17.20	16.60
BTB0.5-MH2.2-70PBLT1	2X35	17.00	18.20	19.70	19.10
BTB0.5-MH2.2-80PBLT1	2X40	19.50	20.70	22.20	21.60

合高(H)	公座单高	母座单高	GENERAL TOLERANCES UNLESS SPECIFIED		H HMT CONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd				
3.0	2.2	2.2	X.±0.50	±1°	PART NO.	TITLE: 0.5 Pitch B型单槽立式			
3.5	2.2	2.7	.X±0.20		BTB0.5—MH2.2—NPBLT1	BTB母座业务图(单高2.2)无焊片点镀金			
4.0	2.2	3.2	.XX±0.10		DESIGN: James	CUSTOMER	SIZE	UNITS	
					CHED: Talen		A4	MM	
5.0	2.6	4.4	MANUFACTURE DWG		APPD: Sophia		SCALE	SHEET	
							N:A	1/1	