




序号	品名	材质
①	0.5 Pitch B型单槽 立式BTB公座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型单槽 立式BTB公座端子	铜合金/表面镀锡/ 表面点镀金

Part No	CKT	A	B	C	D
BTB0. 5-GH2. 6-8PBLT1	2X4	1.50	3.60	4.10	3.60
BTB0. 5-GH2. 6-10PBLT1	2X5	2.00	3.10	4.60	4.10
BTB0. 5-GH2. 6-12PBLT1	2X6	2.50	3.60	5.10	4.60
BTB0. 5-GH2. 6-14PBLT1	2X7	3.00	4.10	5.60	5.10
BTB0. 5-GH2. 6-16PBLT1	2X8	3.50	4.60	6.10	5.60
BTB0. 5-GH2. 6-18PBLT1	2X9	4.00	5.10	6.60	6.10
BTB0. 5-GH2. 6-20PBLT1	2X10	4.50	5.60	7.10	6.60
BTB0. 5-GH2. 6-22PBLT1	2X11	5.00	6.10	7.60	7.10
BTB0. 5-GH2. 6-24PBLT1	2X12	5.50	6.60	8.10	7.60
BTB0. 5-GH2. 6-26PBLT1	2X13	6.00	7.10	8.60	8.10
BTB0. 5-GH2. 6-28PBLT1	2X14	6.50	7.60	9.10	8.60
BTB0. 5-GH2. 6-30PBLT1	2X15	7.00	8.10	9.60	9.10
BTB0. 5-GH2. 6-32PBLT1	2X16	7.50	8.60	10.10	9.60
BTB0. 5-GH2. 6-34PBLT1	2X17	8.00	9.10	10.60	10.10
BTB0. 5-GH2. 6-36PBLT1	2X18	8.50	9.60	11.10	10.60
BTB0. 5-GH2. 6-38PBLT1	2X19	9.00	10.10	11.60	11.10
BTB0. 5-GH2. 6-40PBLT1	2X20	9.50	10.60	12.10	11.60
BTB0. 5-GH2. 6-44PBLT1	2X22	10.50	11.6	13.1	12.60
BTB0. 5-GH2. 6-50PBLT1	2X25	12.00	13.1	14.6	14.10
BTB0. 5-GH2. 6-60PBLT1	2X30	14.50	15.6	17.1	16.60
BTB0. 5-GH2. 6-70PBLT1	2X35	17.00	18.1	19.6	19.10
BTB0. 5-GH2. 6-80PBLT1	2X40	19.50	20.6	22.1	21.60

技术指标:

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
- 温度范围:-40° C~85° C.
- 额定电压:125V, AC.
- 接触电阻:≤0.02 Ω.
- 绝缘电阻:≥100M Ω

合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

GENERAL TOLERANCES UNLESS SPECIFIED		深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
X.±0.50	±1°	PART NO.	TITLE: 0.5 Pitch B型单槽立式 BTB公座业务图(单高2.6)无焊片镀点金	
.X±0.20		BTB0.5-GH2.6-NPBLT1		
.XX±0.10		DESIGN: James	CUSTOMER	SIZE A4
MANUFACTURE DWG		CHED: Talen		UNITS MM
		APPD: Sophia		SHEET N:A 1/1