

1


2

3


4

A


A




TOP VIEW




FRONT VIEW



RIGHT SIDE VIEW




BACK VIEW




LEFT SIDE VIEW

B

B



BOTTOM VIEW

RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE

X09AHIWA1DY1017

1:AU=1U"
3:AU=3U"
4:AU=6U"
5:AU=15U"
6:AU=30U"

PCB SIDE TO PHY



C

D

D

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: RJ JACK
CHECKED		UNIT: mm/in	PART NO.: X09AHIWA1DY1017
APPROVED		SIZE: A4	DWG NO.: X-X09AHIWA1DY1017
		SCALE	PAGE
		N/A	1/1
		REVISION	A1

1

2

3

4