





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.10	阿树




PCB_LAYOUT

Specifications:
Rated Load: DC 12V0.1A
Current rating: 50mA AC / DC
Contact Resistance: $\leq 30m\Omega$
Insulation Resistance: $\geq 100M\Omega$
Withstanding voltage: AC 250V (50Hz) /minute
Temperature range: $-25^{\circ}C \sim +85^{\circ}C$
Action force: 350+50gf
Life: 50000~80000cycles

PAPT NO	TS-CB1157-C-A
Operating Force	C:260gf
Height	H:A:3.8



SCHEMATIC



⑤	Terminal	5	Brass (0.30t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	PA66	
②	Cover	1	Brass	Plating Nickel
①	Keystake	1	PA66	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	$\pm 5^{\circ}$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	TACT SWITCH
PART NO.:	TS-CB1157-C-A
DWG NO.:	X-TS-CB1157-C-A

SCALE	PAGE	REVISION
N/A	1/1	A1