







- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
 3. 额定电压: 50V, AC。
 4. 接触电阻: $\leq 0.03\ \Omega$ 。
 5. 绝缘电阻: $\geq 100\text{M}\ \Omega$ 。



序号	品名	材质
①	0.5 Pitch D型单槽侧插BTB母座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.5 Pitch D型单槽侧插BTB母座端子	铜合金 / 表面点镀金

Part No	CKT	A	B	C	D
BTB0. 5-MH5. 3-4PDCC1	2*2	0.50	2.54	3.50	2.20
BTB0. 5-MH5. 3-6PDCC1	2*3	1.00	3.04	4.00	2.70
BTB0. 5-MH5. 3-8PDCC1	2*4	1.50	3.54	4.50	3.20
BTB0. 5-MH5. 3-10PDCC1	2*5	2.00	4.04	5.00	3.70
BTB0. 5-MH5. 3-12PDCC1	2*6	2.50	4.54	5.50	4.20
BTB0. 5-MH5. 3-14PDCC1	2*7	3.00	5.04	6.00	4.70
BTB0. 5-MH5. 3-16PDCC1	2*8	3.50	5.54	6.50	5.20
BTB0. 5-MH5. 3-18PDCC1	2*9	4.00	6.04	7.00	5.70
BTB0. 5-MH5. 3-20PDCC1	2*10	4.50	6.54	7.50	6.20
BTB0. 5-MH5. 3-22PDCC1	2*11	5.00	7.04	8.00	6.70
BTB0. 5-MH5. 3-24PDCC1	2*12	5.50	7.54	8.50	7.20
BTB0. 5-MH5. 3-26PDCC1	2*13	6.00	8.04	9.00	7.70
BTB0. 5-MH5. 3-28PDCC1	2*14	6.50	8.54	9.50	8.20
BTB0. 5-MH5. 3-30PDCC1	2*15	7.00	9.04	10.00	8.70
BTB0. 5-MH5. 3-32PDCC1	2*16	7.50	9.54	10.50	9.20
BTB0. 5-MH5. 3-34PDCC1	2*17	8.00	10.04	11.00	9.70
BTB0. 5-MH5. 3-36PDCC1	2*18	8.50	10.54	11.50	10.20
BTB0. 5-MH5. 3-38PDCC1	2*19	9.00	11.04	12.00	10.70
BTB0. 5-MH5. 3-40PDCC1	2*20	9.50	11.54	12.50	11.20
.....	...	...	...	...	...
BTB0. 5-MH5. 3-80PDCC1	2*40	19.50	21.54	22.50	21.20

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X. ± 0.50	± 1°	PART NO.	TITLE: 0.5 Pitch D型单槽侧插BTB母座业务图(单高5.3)	
.X ± 0.20		BTB0.5-MH5.3-NPDCC1		
.XX ± 0.10		DESIGN: James	CUSTOMER	SIZE UNITS
MANUFACTURE DWG		CHED: Talen		A4 MM
		APPD: Sophia		SCALE SHEET
				N:A 1/1