



Recommended P.C.B
Layout(±0.05)

Technical Data
Pin(outer sleeve):Brass,machined CuZn38Pb2
Insulator:PPS UL94V-0 colour:black
Current rating:2Amps
Mating pin Ø:0.50mm
Contact resistance:max 10m Ω
Dielectric strength:min 1000V RMS
Operaling temperature:-40°C to+105°C
Soldering temperature:+255°C

X5521W V-2x12 -C35 D35-1000

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series.N0.
- ② Category : W-Wafer
- ③ Welding Board Angle : V-Straight 180°
- ④ Row No-Pin No:2*XX-01P-XXP
- ⑤ Pin Length :C=3.5mm
- ⑥ Pin Length :D=3.5mm
- ⑦ 1000:Type1000

X5521WV-2x12-C35D35-1000	PPS 94V-0	Brass	Tin Gold 1u"	X5521WV
PART N0	Material	Material(Terminal)	Finish(Terminal)	Mates With XKB Pin Header

							DSND		DATE		SCALE: N/A	MODEL TYPE: X5521WV-2x12-C35D35-1000			
Δx					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.:			
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.:			
Δx					4<L ≤ 16	±0.3									
Δx					16<L ≤ 63	±0.4	APPD		DATE		SIZE: A4				
MARK	DESCRIPTION			DATE	REVISED	APPROVED									L > 63
REVISIONS							UNSPECIFIED TOLERANCES						XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn															
												WEIGHT	SHEET	REVISION	
												1.0g	1/1	A0	