

3-2. OPERATION TEMPERATURE:  $-40^{\circ}\text{C}$  To  $+85^{\circ}\text{C}$ :





| Ass'y High(H) | Plastic High |             |
|---------------|--------------|-------------|
|               | Male (H1)    | Female (H2) |
| 1.50          | 1.14         | 1.40        |
| 2.00          | 1.14         | 1.90        |
| 2.50          | 1.14         | 2.40        |
| 3.00          | 1.14         | 2.90        |
| 3.50          | 1.14         | 3.40        |
| 4.00          | 1.14         | 3.90        |

High (H)  
1.5=1.50mm  
2.0=2.00mm  
2.5=2.50mm  
3.0=3.00mm

[illegible]

|      |           |      |          |                                                |        |
|------|-----------|------|----------|------------------------------------------------|--------|
| 2    | Housing   | 1    | LCP      | Glass:30%                                      | Black  |
| 1    | Terminal  | N    | C5240ESH | Ni 50-90u"UNDERPLATING,<br>GOLD FLASH OVER ALL |        |
| ITEM | Part Name | Q'TY | MATERIAL | MATERIAL                                       | REMARK |



|           |                        |                    |                   |                   |                                                                                                                                                       |                  |                          |              |     |
|-----------|------------------------|--------------------|-------------------|-------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|--------------------------|--------------|-----|
|           |                        |                    | GENERAL TOLERANCE | 制 图<br>DRAWING    |  <b>深圳市华灿天禄电子有限公司</b><br>ShenzhenhuacantianluELECTRONICS CO.,LTD |                  |                          |              |     |
|           |                        |                    | DIM TOL           | 审 核<br>CHECK      |                                                                                                                                                       |                  |                          |              |     |
|           |                        |                    | X. X ±0.30        | 批 准<br>APPROVAL   |                                                                                                                                                       | 产品名称<br>TITLE    | 0.4 双槽 贴片 母座 (BTB)       | 版 本<br>REV.  | A   |
|           |                        |                    | X. XX ±0.20       | 比 例<br>SCALE      |                                                                                                                                                       | 产品料号<br>PART NO. | HC-PBB40C-NDS-0.4V-XX-02 | 单 位<br>UNITS | mm  |
| 1         | 初版发行                   |                    | X. XXX ±0.10      |                   |                                                                                                                                                       |                  |                          |              |     |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日 期<br>MODIFY DATE | Angle ±3.0°       | 投 影<br>Projection |                                                                  | 材 料<br>MATERIAL  |                          | 页 次<br>SHEET | 1/1 |