





序号	品名	材质
1	0.5 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0 颜色:黑色
2	0.5 Pitch双槽立式BTB母座端子	铜合金/表面点镀金
3	0.5 Pitch双槽立式BTB母座吸盖	LCP UL94 V-0 颜色:黑色.

PIN NO	PIN	DIM A	DIM B	DIM C	DIM D
BTB0. 5-MH2. 2-8PALT2	8	1.50	2.55	4.70	4.00
BTB0. 5-MH2. 2-10PALT2	10	2.00	3.05	5.20	
BTB0. 5-MH2. 2-12PALT2	12	2.50	3.55	5.70	
BTB0. 5-MH2. 2-14PALT2	14	3.00	4.05	6.20	
BTB0. 5-MH2. 2-16PALT2	16	3.50	4.55	6.70	
BTB0. 5-MH2. 2-18PALT2	18	4.00	5.05	7.20	
BTB0. 5-MH2. 2-20PALT2	20	4.50	5.55	7.70	
BTB0. 5-MH2. 2-22PALT2	22	5.00	6.05	8.20	
BTB0. 5-MH2. 2-24PALT2	24	5.50	6.55	8.70	
BTB0. 5-MH2. 2-26PALT2	26	6.00	7.05	9.20	
BTB0. 5-MH2. 2-28PALT2	28	6.50	7.55	9.70	
BTB0. 5-MH2. 2-30PALT2	30	7.00	8.05	10.20	
BTB0. 5-MH2. 2-32PALT2	32	7.50	8.55	10.70	8.00
BTB0. 5-MH2. 2-34PALT2	34	8.00	9.05	11.20	
BTB0. 5-MH2. 2-36PALT2	36	8.50	9.55	11.70	
BTB0. 5-MH2. 2-38PALT2	38	9.00	10.05	12.20	
BTB0. 5-MH2. 2-40PALT2	40	9.50	10.55	12.70	
BTB0. 5-MH2. 2-44PALT2	44	10.50	11.05	13.70	
BTB0. 5-MH2. 2-50PALT2	50	12.00	13.05	15.20	
BTB0. 5-MH2. 2-60PALT2	60	14.50	15.55	17.70	
BTB0. 5-MH2. 2-70PALT2	70	17.00	18.05	20.20	
BTB0. 5-MH2. 2-80PALT2	80	19.50	20.55	22.70	
BTB0. 5-MH2. 2-100PALT2	100	24.50	25.55	27.70	

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围:-40° C~85° C.
3. 额定电压:50V, AC.
4. 接触电阻:≤0.02 Ω.
5. 绝缘电阻:≥100M Ω

适用线路板

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTconn Shenzhen Huamingtong Electronics Co., Ltd		
X.±0.50	±1°	PART NO.	TITLE:	
.X±0.20		BTB0.5-MH2.2-NPALT2	0.5 Pitch双槽立式BTB母座无柱(单高2.2)	
.XX±0.10		DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
APPD: Sophia		APPD: Sophia		MM
			SCALE	SHEET
			N:A	1/1