








技术指标 (Technical Index):


1. 工作温度 (Temperature range): $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$.
2. 适用线规 (Apply to gauge): AWG#28~#24
3. 额定电压 (Rated voltage): 250V DC/AC(rms).
4. 额定电流 (Rated current): 3.0A AC, DC.
5. 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
6. 耐压值 (Dielectric withstanding voltage): 800V AC/minute.
7. 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\Omega$.



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)




2P 结构样式



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
D-PHD2.0-W2-M2P42	2*2	2.00	6.00
D-PHD2.0-W2-M3P42	2*3	4.00	8.00
D-PHD2.0-W2-M4P42	2*4	6.00	10.00
D-PHD2.0-W2-M5P42	2*5	8.00	12.00
D-PHD2.0-W2-M6P42	2*6	10.00	14.00
D-PHD2.0-W2-M7P42	2*7	12.00	16.00
D-PHD2.0-W2-M8P42	2*8	14.00	18.00
D-PHD2.0-W2-M9P42	2*9	16.00	20.00
D-PHD2.0-W2-M10P42	2*10	18.00	22.00
D-PHD2.0-W2-M11P42	2*11	20.00	24.00
D-PHD2.0-W2-M12P42	2*12	22.00	26.00
D-PHD2.0-W2-M13P42	2*13	24.00	28.00
D-PHD2.0-W2-M14P42	2*14	26.00	30.00
D-PHD2.0-W2-M15P42	2*15	28.00	32.00
D-PHD2.0-W2-M16P42	2*16	30.00	34.00
D-PHD2.0-W2-M18P42	2*18	34.00	38.00
D-PHD2.0-W2-M20P42	2*20	38.00	42.00

1	PHD卧贴WTB胶芯	LCP UL94V-0 本色			
2	PHD卧贴(连绕)端子	铜合金/表面镀锡			
序号	名称	材质			
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.25	X.*±3	PART NO.	TITLE: 2.0 Pitch D型双排卧贴		
.XX±0.12	X.X*±0.5*	D-PHD2.0-W2-MNP42			
.XXX±0.05		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava			
FINISH	— — —			SCALE N:A	SHEET 1/1