






技术指标:

1. 温度范围: $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐电压: 800V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 3A AC, DC.

材料

1. 塑胶: PA66 白色

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

型号	CKT	A	B	C
C-PHB2.0-2-M2P12	2*2	2.00	7.00	2.90
C-PHB2.0-2-M3P12	2*3	4.00	9.00	3.10
C-PHB2.0-2-M4P12	2*4	6.00	11.00	4.30
C-PHB2.0-2-M5P12	2*5	8.00	13.00	6.30
C-PHB2.0-2-M6P12	2*6	10.00	15.00	8.30
C-PHB2.0-2-M7P12	2*7	12.00	17.00	6.30
C-PHB2.0-2-M8P12	2*8	14.00	19.00	8.30
C-PHB2.0-2-M9P12	2*9	16.00	21.00	14.30
C-PHB2.0-2-M10P12	2*10	18.00	23.00	14.30
C-PHB2.0-2-M11P12	2*11	20.00	25.00	14.30
C-PHB2.0-2-M12P12	2*12	22.00	27.00	14.30
C-PHB2.0-2-M13P12	2*13	24.00	29.00	14.30
C-PHB2.0-2-M14P12	2*14	26.00	31.00	14.30
C-PHB2.0-2-M15P12	2*15	28.00	33.00	14.30
C-PHB2.0-2-M16P12	2*16	30.00	35.00	14.30
C-PHB2.0-2-M22P12	2*22	42.00	47.00	14.30

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.*±5°	PART NO.	TITLE: PHB2.0公头胶壳		
.XX±0.25	X.X°±1°	C-PHB2.0-2-MNP12			
.XXX±0.15		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava		SCALE	SHEET
FINISH	— — —			N:A	1/1