



PCB Hole Layout



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:600V AC/minute

耐受电压: 600V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X9555 W V - 2x08 A - PT V01
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Row No.Pin No:2xXX-2x03~2x12P
- 5.Special No:A-Ejector Header
- 6.Material:PB-PBT; 6T-PA6T;9T-PA9T; LP-LCP UL94V-0
- 7.Plating:V01-Gold Flash or SN-Tin Plated

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x03	5.08	26.82	2x13	30.48	52.22
2x04	7.62	29.36	2x15	35.56	57.30
2x05	10.16	31.90	2x17	40.64	62.00
2x07	15.24	36.98	2x20	48.26	70.00
2x08	17.78	39.52	2x25	60.96	82.70
2x09	42.06	42.06	2x30	73.66	95.40
2x10	22.86	44.60	2x32	78.74	100.48
2x12	27.94	49.68	/		

X9555WV-2x08A-PTV01	PBT	Copper Alloy	X9555H
PART N0	Material	Material(Pin)	Suitable XKB Housing

ΔX	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					
ΔX					
ΔX					
MARK					
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connector
DWN	VIEW:	PART NO.: X9555WV-2x08A-PTV01
CHKD	UNIT: mm/in	DWG NO.: X-X9555WV-2x08A-PTV01
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0